



## Biaxially Oriented PA-film

### Technical Data Sheet

#### BIAXIS BOPA 10 STD

##### General Properties

	Unit	Value	Standard / Test method
Thickness	µm	10 +/-10%	DIN 53370
Melting Point	°C	220 +/- 2	ISO 3146-C / DSC
Density	g/cm <sup>3</sup>	1,15 +/- 0,01	ISO 1183
Haze	%	≤ 4	ASTM D 1003
Shrinkage	% (MD / TD), 160°C, 5 min	≤ 2,5 / ≤ 2,5	DIN EN ISO 11501
Friction (non-treated)	Stat. / dyn.; Film / Alu	< 0,40 / < 0,40	DIN EN ISO 8295, ASTM D 1894
Treatment level	dynes/cm (treated / not treated)	> 45 / > 37	DIN ISO 8296, ASTM D 2578

##### Mechanical Properties

	Unit	Value	Standard / Test method
Tensile Strength	N/mm <sup>2</sup> (MD / TD)	>210 / >210	DIN EN ISO 527, ASTM D 882
Elongation at Break	% (MD / TD)	115 / 90 +/- 30	DIN EN ISO 527, ASTM D 882
Puncture Resistance	N	>5	DIN EN 14477
Flex-Crack	holes / dm <sup>2</sup>	<1	ASTM F 392-74

All mechanical values are according to 2 sigma level

##### Barrier Properties

	Unit	Value	Standard / Test method
O <sub>2</sub> Transmission Rate	cm <sup>3</sup> / m <sup>2</sup> , 24h, bar	85 *)	DIN 53380-3, ASTM D 3985 23°C, 0% RH
		45 *)	DIN 53380-3, ASTM D 3985 23°C, 50% RH
WV Transmission Rate	g/m <sup>2</sup> , 24h	70 *)	DIN 53122, ASTM E 96 23°C, 85% RH

\*) Typical value

All the rawmaterials used in Biais films fulfill the requirements for food packaging as specified by the latest EU- and FDA-regulations.

The recommendations and data given are based on our experience to date, but no liability can be assumed in connection with their usage.

Values are valid on print date 3.12.2021

BIAXIS BOPA STD  
29.4.2016

Postal Address

Telephone

Telefax

VAT Reg.No.

**Biaxis Oy Ltd.**  
Teknikonkatu 2  
FIN-15520 LAHTI  
FINLAND

+358 (0)20 510 312  
E-mail:info@biaxis.com

+358 (0)20 510 3500

FI01161156

Trade Reg. No.  
189.266